

**Garant**
**TNMG 160404, Grade: HB7035-1**


### Order data

Order number	251542 HB7035-1
GTIN	4045197874740
Item class	21G

### Technical description

Cutting speed $v_c$ main application	100 - 320 m/min
Cutting depth $a_p$	0.5 - 5 mm
Cutting conditions	heavily interrupted
Feed $f$	0.2 - 0.5 mm/rev.
Main application	P
Grade	HB7035-1
Chip breaker	SM
Corner radius	0.4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Tolerance	M
Type of product	Indexable insert for turning