

**Garant****TNMG 160408, Grade: HB7035-1**

## Order data

Order number	251544 HB7035-1
GTIN	4045197874764
Item class	21G

## Description

TN.G 160408 HB7035-1 Grade: HB7035-1  
Chip breaker: SM  
Tolerance: M  
Cutting depth  $a_p$ : 0.5 - 5 mm  
Feed  $f$ : 0.2 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 100 - 320 m/min

## Technical description

Chip breaker	SM
Feed $f$	0.2 - 0.5 mm/rev.
Cutting depth $a_p$	0.5 - 5 mm
Main application	P
Cutting conditions	heavily interrupted
Corner radius	0.8 mm
Cutting speed $v_c$ main application	100 - 320 m/min

Grade	HB7035-1
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning