

Garant**VBMT 110304, Grade: HB7035-1****Order data**

| | |
|--------------|-----------------|
| Order number | 261144 HB7035-1 |
| GTIN | 4045197874788 |
| Item class | 21G |

Description

VBMT 110304 HB7035-1 Grade: HB7035-1
Chip breaker: SS
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.05 - 0.2 mm/rev.
Cutting speed v_c main application: 120 - 350 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Corner radius | 0.4 mm |
| Cutting speed v_c main application | 120 - 350 m/min |
| Feed f | 0.05 - 0.2 mm/rev. |
| Grade | HB7035-1 |
| Cutting depth a_p | 0.2 - 1.5 mm |
| Cutting conditions | heavily interrupted |
| Chip breaker | SS |

| | |
|-------------------------------|------------------------------|
| Main application | P |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | VBMT 110304 |
| Number of changes/inserts | 2 |
| Type of product | Indexable insert for turning |