

Garant**VC.T 160402, Grade: HB7035-1**

Order data

Order number	261370 HB7035-1
GTIN	4045197874887
Item class	21G

Description

VCMT 160402 HB7035-1 Grade: HB7035-1
Chip breaker: SS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.05 - 0.2 mm/rev.
Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting conditions	heavily interrupted
Chip breaker	SS
Grade	HB7035-1
Corner radius	0.2 mm
Main application	P
Feed f	0.05 - 0.2 mm/rev.

Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	120 - 350 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VCMT 160402
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning