

Fine thread “No Go” ring gauge 6g, M × pitch: 58X1,5**Order data**

Order number	486210 58X1,5
GTIN	2050001669889
Item class	48B

Description**Version:**

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Thread	M58
Thread pitch	1.5 mm
Tolerance class	6g
Calibration	L12

Tolerance zone	g
Type of gauge	"No Go" gauge
Thread type	MF
Standard	DIN 13
Quality	6
Type of product	Thread "No Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 60 mm	028600 60