

Garant
VNMG 160408, Grade: HB7035-1


Order data

Order number	251734 HB7035-1
GTIN	4045197874955
Item class	21G

Description

VNMG 160408 HB7035-1 Grade: HB7035-1
 Chip breaker: SS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.08 - 0.4 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting depth a_p	0.3 - 2 mm
Cutting conditions	heavily interrupted
Grade	HB7035-1
Corner radius	0.8 mm
Cutting speed v_c main application	120 - 350 m/min
Main application	P
Chip breaker	SS

Feed f	0.08 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Type of product	Indexable insert for turning