

Fine thread “No Go” ring gauge 6g, M × pitch: 18X1



Order data

Order number	486210 18X1
GTIN	2050001036131
Item class	48B

Description

Version:

The ground first thread lead chamfer (from 1 mm pitch) removes contamination in the component and prevents premature fracture of the first full thread lead chamfer.

Design to **DIN 2279 – 2299**.

Application:

For metric ISO fine threads, right-hand DIN 13.

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, and NPT threads as well as left-hand threads available on request.

Technical description

Thread	M18
Thread pitch	1 mm
Tolerance class	6g
Calibration	L12

Type of gauge	"No Go" gauge
Tolerance zone	g
Standard	DIN 13
Thread type	MF
Quality	6
Type of product	Thread "No Go" ring gauge

Services

Calibration Thread ring gauge maximum \varnothing 20 mm	028600 20
DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100