



## HOLEX CleverDrill HSS jobber drill set No. 114030 in a case, uncoated, Type: 1-6



### Order data

Order number	115050 1-6
GTIN	4045197871787
Item class	12B

### Description

#### Version:

Composed of jobber drills DIN 338.

**HOLEX CleverDrill:** Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

#### Note:

Size 13.2 – 20: With stepped shank  $\varnothing$  12.7 mm.

Through-coolant: no

Shank: Plain shank

Drill range: 1 - 6 mm

Number of drills: 51

Incremental steps of drills: 0.1 mm

### Technical description

Incremental steps of drills	0.1 mm
Drill range	1 - 6 mm

Number of drills	51
Shank	Plain shank
Number of cutting edges Z	2
Series	HOLEX CleverDrill
Tool material	HSS
Standard	DIN 338
Type	N
Tolerance nominal $\varnothing$	h8
Point angle	130°
Through-coolant	no
with case	yes
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	60 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K
CuZn	suitable	40 m/min	N
Oil	suitable		

wet maximum

suitable

**Accessories**HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,3

114030 5,3

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,4

114030 4,4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
2

114030 2

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,2

114030 4,2

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,6

114030 5,6

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,4

114030 1,4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,1

114030 5,1

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,7

114030 3,7

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,8

114030 4,8

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,2

114030 3,2

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,1

114030 4,1

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,2

114030 5,2

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,9

114030 3,9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,6

114030 3,6

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,5

114030 1,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1	114030 1
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,8	114030 3,8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,7	114030 2,7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,6	114030 2,6
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,4	114030 2,4
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,6	114030 4,6
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1,8	114030 1,8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,5	114030 4,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 5,7	114030 5,7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 5,5	114030 5,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 5,8	114030 5,8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,3	114030 3,3
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,7	114030 4,7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,5	114030 2,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1,2	114030 1,2
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1,7	114030 1,7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,9	114030 2,9
	114030 4,9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,9

114030 1,9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5

114030 5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,4

114030 3,4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
2,3

114030 2,3

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,1

114030 1,1

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,1

114030 3,1

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4

114030 4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
6

114030 6

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3,5

114030 3,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,3

114030 1,3

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
2,8

114030 2,8

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
3

114030 3

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
2,2

114030 2,2

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,9

114030 5,9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
1,6

114030 1,6

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
4,3

114030 4,3

114030 5,4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
5,4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)  
2,1

114030 2,1