



HOLEX CleverDrill HSS jobber drill set No. 114030 in a case, uncoated, Type: 1-10,5



Order data

Order number	115050 1-10,5
GTIN	4045197875419
Item class	12B

Description

Version:

Composed of jobber drills DIN 338.

HOLEX CleverDrill: Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Note:

Size 13.2 – 20: With stepped shank \varnothing 12.7 mm.

Through-coolant: no

Shank: Plain shank

Drill range: 1 - 10.5 mm

Number of drills: 24

Tapping hole \varnothing : 3.3; 4.2; 6.8; 10.2 mm

Incremental steps of drills: 0.5 mm

Technical description

Number of drills	24
------------------	----

Shank	Plain shank
Drill range	1 - 10.5 mm
Incremental steps of drills	0.5 mm
Tapping hole Ø	3.3; 4.2; 6.8; 10.2 mm
Number of cutting edges Z	2
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Standard	DIN 338
Type	N
Tolerance nominal Ø	h8
Point angle	130 °
Through-coolant	no
with case	yes
Colour ring	without
Type of product	Jobber drill

Accessories

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 9 mm or inch	114030 9
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 6,8 mm or inch	114030 6,8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2,5 mm or inch	114030 2,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,3 mm or inch	114030 3,3
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2 mm or inch	114030 2
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 7,5 mm or inch	114030 7,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,5 mm or inch	114030 3,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 5 mm or inch	114030 5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 8 mm or inch	114030 8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 6,5 mm or inch	114030 6,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 5,5 mm or inch	114030 5,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 10,2 mm or inch	114030 10,2
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1 mm or inch	114030 1
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4 mm or inch	114030 4
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 8,5 mm or inch	114030 8,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 1,5 mm or inch	114030 1,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 9,5 mm or inch	114030 9,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 7 mm or inch	114030 7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,5 mm or inch	114030 4,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 10 mm or inch	114030 10
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 6 mm or inch	114030 6
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 10,5 mm or inch	114030 10,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,2 mm or inch	114030 4,2
	114030 3

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
3 mm or inch
