



HOLEX CleverDrill HSS jobber drill set No. 114030 as a refill set, uncoated, Type: 1-10,5



Order data

Order number	115055 1-10,5
GTIN	4045197875495
Item class	12B

Description

Version:

Composed of jobber drills DIN 338.

HOLEX CleverDrill: Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Note:

Size 13.2 – 20: With stepped shank \varnothing 12.7 mm.

Through-coolant: no

Shank: Plain shank

Drill range: 1 - 10.5 mm

Number of drills: 24

Tapping hole \varnothing : 3.3; 4.2; 6.8; 10.2 mm

Incremental steps of drills: 0.5 mm

Technical description

Shank	Plain shank
Number of drills	24
Drill range	1 - 10.5 mm
Incremental steps of drills	0.5 mm
Tapping hole \varnothing	3.3; 4.2; 6.8; 10.2 mm
Number of cutting edges Z	2
Series	HOLEX CleverDrill

Coating	uncoated
Tool material	HSS
Standard	DIN 338
Type	N
Tolerance nominal Ø	h8
Point angle	130 degrees
Through-coolant	no
with case	no
Colour ring	without
Type of product	Jobber drill

Accessories

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 6,8 mm or inch	114030 6,8
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 10,2 mm or inch	114030 10,2
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 7,5 mm or inch	114030 7,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,3 mm or inch	114030 3,3
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 7 mm or inch	114030 7
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 4,5 mm or inch	114030 4,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3 mm or inch	114030 3
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 3,5 mm or inch	114030 3,5
HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch) 2 mm or inch	114030 2
	114030 5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
5 mm or inch

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
9 mm or inch

114030 9

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
5,5 mm or inch

114030 5,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
6,5 mm or inch

114030 6,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
2,5 mm or inch

114030 2,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
4 mm or inch

114030 4

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
1 mm or inch

114030 1

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
10,5 mm or inch

114030 10,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
1,5 mm or inch

114030 1,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
8 mm or inch

114030 8

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
9,5 mm or inch

114030 9,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
8,5 mm or inch

114030 8,5

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
6 mm or inch

114030 6

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
10 mm or inch

114030 10

HOLEX CleverDrill HSS jobber drill N Ø DC h8 (mm or inch)
4,2 mm or inch

114030 4,2