

Pipe threads "No Go" ring gauge, Threads: G1/4in



Order data

Order number	486250 G1/4
GTIN	2050001036308
Item class	48B

Description

Version:

Plug thread gauges to DIN EN ISO 228-2. Ring thread gauges tolerance class A.

"No Go" gauges marked red.

Standard:

DIN EN ISO 228

Note:

Thread gauges for other diameters available on request.

Technical description

Tolerance class	A
Threads per inch	19
Thread	G1/4
Thread Ø	13.16 mm
Calibration	L12
Type of gauge	"No Go" gauge

Tolerance zone	A
Standard	DIN 228
Thread type	G
Type of product	Thread "No Go" ring gauge

Services

DAkkS calibration Thread "Go" ring gauge maximum \varnothing 100 mm	028640 100
Calibration Thread ring gauge maximum \varnothing 20 mm	028600 20