

LOCTITE**Instant adhesive, 20 g, Manufacturer ID: 401_IG**

Order data

Order number	083352 401_IG
GTIN	4058093010914
Item class	04L

Description

Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

Note:

Not available in all countries. Express delivery not possible.

Technical description

Tensile shear strength	20 N/mm ²
Touch dry after	3 - 10 s
Manufacturer's designation	401
Labelling of hazardous substances	GHS07: Exclamation mark
Dynamic viscosity	70 - 110 mPas
Storage temperature	2 - 8 °C
Shape	liquid

Operating temperature range	-40 - 120 °C
Colour	transparent
Working life after date of manufacture	24 mo
Density	1.05 g/cm ³
Suitable for material	wood
Suitable for material	Fabric
Suitable for material	Elastomer
Suitable for material	Leather
Suitable for material	Plastic
Suitable for material	Paper
Suitable for material	Metal
Chemical basis	Ethyl cyanoacrylate
Capacity	20 ml
Maximum gap size	0.15 mm
Product name attribute	20 g
Type of product	Instant adhesive