

LOCTITE.**Instant adhesive, 20 g, Manufacturer ID: 454_IE**

Order data

Order number	083352 454_IE
GTIN	4058093008911
Item class	04L

Description

Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

Note:

Not available in all countries. Express delivery not possible.

Technical description

Manufacturer's designation	454
Touch dry after	5 - 10 s
Labelling of hazardous substances	GHS07: Exclamation mark
Tensile shear strength	20.9 N/mm ²
Storage temperature	2 - 8 °C
Shape	Gel
Operating temperature range	-40 °C

Characteristics	anaerobic adhesive
Characteristics	does not penetrate into workpiece surface
Suitable for material	Paper
Suitable for material	Plastic
Suitable for material	wood
Suitable for material	Leather
Suitable for material	cardboard
Suitable for material	Metal
Suitable for material	Elastomer
Suitable for material	porous materials
Density	1.05 g/cm ³
Working life after date of manufacture	24 mo
Chemical basis	Ethyl cyanoacrylate
Colour	transparent
Capacity	20 ml
Maximum gap size	0.15 mm
Product name attribute	20 g
Type of product	Instant adhesive