



Precision angle bender complete with accessories, maximum component height: 100mm



Order data

Order number	823600 100
GTIN	2050001933072
Item class	86K

Description

Version:

Easy to operate, powerful bending machine for precise bending of various profiles up to 180°. Positive and secure clamping of the profiles. Good repetition accuracy of the bend thanks to the precise bending and clamping jig. Integral **angle and length stops for quick working** with exact bending results. Smooth operation even with solid profiles due to a **needle-bearing turntable** (size 60 and 100).

Application:

Precise and user-friendly hot and cold bending (bending angle 0 – 180°), both with angular bending edges and also with various bending radii.

Suitable for:

Workbench

Supplied with:

1 bending plate (r = 2 mm), 90° No. 823603 size 2, 1 angle stop, 1 length stop, 1 operating handle.

Note:

Further bending plates can be found under No. 823601 – 823604.

Technical description

maximum component height	100 mm
maximum bending capacity for round material (cold) Ø	18 mm
Depth	240 mm

maximum bending capacity for flat material (cold)	100×7 / 18×18 mm
Weight	43.9 kg
Height	205 mm
maximum bending capacity for flat material (hot)	100×10 / 22×22 mm
Width	465 mm
Type of product	Bending machine

Accessories

Additional clip	823604
Bending tool Radius 15	823603 15
Bending tool Radius 10	823603 10
Bending tool Radius 5	823603 5
Bending tool Radius 2	823603 2