

**“Revo KRE” body clamp, Jaw capacity a: 600mm****Order data**

Order number	860291 600
GTIN	4008158040134
Item class	83K

Description**Version:**

Beam of bright drawn steel, electro-galvanised. Moving jaw with double anti-slip protection. Smooth running steel spindle with trapezoidal thread, burnished. Metal, reinforced plastic housing. Clamping forces up to **8000 N**.

- **Extremely large clamping faces with removable protective caps**
- **Workpiece protection inserts, removable**
- **Turning the bottom jaw over converts the clamp into a spreader**
- **2-component handle with hex socket (6 AF) for easy application of the clamping force**

Application:

The jaws surround the beam, thus can be used to clamp at the sides and the rear. This allows access to clamping positions inaccessible to conventional clamps. Can be converted to spreading, **no tools required**.

Note:

Successor product to No. 860290.

Technical description

Weight	2.76 kg
--------	---------

Data sheet

Spreading width e	255 - 730 mm
Cross section of the slide rail	29×9 mm
Jaw capacity a	600 mm
Throat b	95 mm
Manufacturer's designation	REVO KRE
maximum clamping force	8000 N
Type of product	Clamp