


**C-clamp, Jaw capacity: 40mm****Order data**

Order number	861550 40
GTIN	4008158019178
Item class	83K

Description**Version:**

C-shape, forged steel, tempered. Strong spindle with trapezoidal thread and movable special jaw anvil.

Application:

Maximum clamping pressure up to 22,000 N.

Technical description

Throat	40 mm
Jaw capacity	40 mm
Type of product	Clamp