

**Abrasive cloth (A) brown, very flexible KK 114 F, 230×280 mm, Grit: 40****Order data**

Order number	556900 40
GTIN	4018875000373
Item class	56V

Description**Version:**

Densely woven cotton fabric, evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Very good grain adhesion, high abrasive performance and long working life. **Sheet size 230×280 mm.**

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications.** This grade is particularly supple, resistant to oil and petroleum and can be torn in longitudinal direction to yield clean edges without fraying.

Application:

Universally applicable, primarily for rubbing down by hand (for rubber sanding block see No. 557600).

Technical description

Grit designation	coarse
Grit	40
Manufacturer's designation	KK 114 F
Series	KK114F
Grinding media	Standard Aluminium Oxide
Grinding medium code	A
Sanding disc width	280 mm

Sanding disc length	230 mm
Product name attribute	230×280 mm
Type of product	Abrasive cloth

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Steel backing plate	556950
Rubber sanding block	557600