

3M Scotch-Brite™

Abrasive fleece hand pads, set of 25 pieces Durable Flex, 114×228 mm, Fleece structure: 1000**Order data**

| | |
|--------------|---------------|
| Order number | 556145 1000 |
| GTIN | 8410001134420 |
| Item class | 53M |

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

Flexible high-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **more aggressive abrasive characteristics**, a very long working life without clogging and an even **more uniform finish**. The **enormous flexibility** enables use even in inaccessible places.

Advantage:

- **Adapts to the shape of the component.**
- **The open structure prevents clogging and reduces heat development.**
- **Consistent reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

For manual cleaning and finishing, ideal substitute for steel wool products. **Fine / ultra fine:** for cleaning delicate surfaces, for repairing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Supplied with:

Pack of 25 hand pads.

Technical description

| | |
|-----------------|------------|
| Grit equivalent | 600 - 1000 |
|-----------------|------------|

| | |
|---|---------------------|
| Grit designation | very fine |
| Colour | grey |
| Fleece structure | 1000 |
| 3M designation | DF |
| Version | S Ultra Fine |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Width | 114 mm |
| Length | 228 mm |
| Product name attribute | 114×228 mm |
| Type of product | Abrasive fleece pad |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Stone | suitable only under restricted conditions | | |
| Paint | suitable | | |
| Uni | suitable | | |

| | |
|-------------|---|
| wet maximum | suitable only under restricted conditions |
| dry | suitable |

Accessories

| | |
|------------|--------|
| Hand block | 556020 |
| Mandrel | 556030 |