



Abrasive cloth (A) brown, very flexible KK 114 F, 230×280 mm, Grit: 600



Order data

Order number	556900 600
GTIN	4002748327452
Item class	56V

Description

Version:

Densely woven cotton fabric, evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Very good grain adhesion, high abrasive performance and long working life. **Sheet size 230×280 mm.**

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications.** This grade is particularly supple, resistant to oil and petroleum and can be torn in longitudinal direction to yield clean edges without fraying. Type **Starcke 531 JFF, highly flexible, ideal for rubbing down fittings.**

Application:

Universally applicable, primarily for rubbing down by hand (for rubber sanding block see No. 557600).

Technical description

Grit designation	polishing
Grit	600
Manufacturer's designation	Thickness 531 JFF,
Series	KK114F
Grinding media	Standard Aluminium Oxide
Grinding medium code	A

Sanding disc width	280 mm
Sanding disc length	230 mm
Product name attribute	230×280 mm
Type of product	Abrasive cloth

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Rubber sanding block	557600
Steel backing plate	556950

