


STARCKE®
Fabric velour-backed abrasive disc (ZA), Ø 115 mm, Grit: 80

Order data

Order number	567605 80
GTIN	4002748779886
Item class	56Z

Description
Version:

Extremely robust 341XK velour-backed abrasive disc, on **reinforced tear-resistant cotton fabric backing**. Newly developed bonding system with Zirconium Aluminium Oxide (**ZA**). The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

Application:

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

Versatile application in **coarse and fine grinding of metals**.

Note:

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

Technical description

Grit	80
Disc Ø	115 mm
Manufacturer's designation	341XK
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %

Product name attribute	Ø 115 mm
Propulsive equipment	Angle grinder
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		

Accessories

Hook and loop backing pad,M14 External Ø 115 mm	567760 115
Hook and loop polishing pad,M14 External Ø 115 mm	567762 115