



Driven tool, radial, standard pin, ER25, Type: 30-25-LIK



Order data

Order number	319931 30-25-LIK
GTIN	4045197877086
Item class	31W

Description

Version:

For use on **disc turrets**. Left-hand version, i.e. machining in the direction of the main spindle.

Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

Standard alignment rail (pin).

Version IKD – with ceramic seal set, pressures up to 70 bar, with full dry-run capability.

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**.

Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via a coolant tube, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

Advantage:

- **Weight- and geometry-optimized design.**
- **Process reliability through high-quality components, longevity.**
- **High torque transmission.**
- **100% control – each driven tool is subjected to a run-in programme.**
- **Internal cooling: specially developed and patented seal.**

Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

Suitable for :

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

Optional extras:

Suitable inserts, Varia VX No. 319802 – 319888, ER collets No. 308941 – 309878, ER chuck keys No. 309680 – 309745.

Note:

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: www.hoffmann.ews-tools.com**
- **IC tools (with through cooling) will not run dry with standard seal, coolant filtering < 50 µm.**
- **Recommendation: Tighten version VARIA VX with a torque tool (max. 6 Nm).**

Tool clamping: ER25

l₁: 126 mm

b₁: 67 mm

b₂: 59.5 mm

h₁: 64 mm

x: 126 mm

Cooling: internal

Technical description

Cooling	internal
x	126 mm
l ₁	126 mm
h ₁	64 mm
b ₁	67 mm
b ₂	59.5 mm
Adapter	ER25
VDI size	30
Tool clamping	ER25

Accessories

Varia collet chuck VARIA VX4 for ER collets 25 ER	319804 25
Varia collet chuck VARIA VX3 for ER collets 25 ER	319802 25