

SWISS TOOLS

Toolholders axial single, left-hand, PSC 80, for toolholder square: 32mm



Order data

Order number	318942 32
GTIN	2050001930040
Item class	36D

Description

Version:

With adjustable cooling nozzle with internal thread.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request.

Technical description

Clamping length L ₁	98 mm
External Ø D	110 mm
for toolholder square	32 mm
Overhang dimension A	140 mm
B	55 mm
Adapter	PSC 80
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Pin vice

