

SWISS TOOLS

Boring bar holder, PSC 80, Clamping \varnothing D1: 20 mm



Order data

Order number	318889 20
GTIN	2050001921864
Item class	36D

Description

Application:

For mounting boring bars.

For use on lathes and milling centres.

Note:

PSC clamping stud on request.

Through-coolant: yes

Overhang dimension A: 98 mm

External \varnothing D: 44 mm

L₁: 68 mm

Technical description

L ₁	68 mm
Clamping \varnothing D ₁	20 mm
External \varnothing D	44 mm
Overhang dimension A	98 mm
Adapter	PSC 80
Arbor standard	ISO 26623-2
Through-coolant	yes
Type of product	Side lock arbor

