

**Garant****Boring bar holder slotted, HSK-T 63, Clamping  $\varnothing$  D1: 20mm****Order data**

Order number	318831 20
GTIN	4045197905192
Item class	31G

**Description****Version:**

**GARANT** - more stability and vibration damping effect due to wrapping around the boring bar.

**Application:**

For mounting boring bars.

For use on lathes and milling centres.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	20 mm
External $\varnothing$ D	55 mm
Overhang dimension A	105 mm
L <sub>1</sub>	79.05 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Side lock arbor