

Garant**eco toolholder radial, HSK-T 63, for toolholder square: 25mm**

Order data

Order number	318625 25
GTIN	4045197893260
Item class	31G

Description

Version:

With adjustable cooling nozzle with internal thread.

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT eco.

Application:

For mounting ISO toolholders with square shanks.

For mounting ISO toolholders with square shanks.

Note:

With pass-through shim. Suitable for toolholders with shank 20 **and** 25 mm.

Technical description

Overhang dimension A	90 mm
Clamping length L ₁	88 mm
B	40 mm
for toolholder square	25 mm
External Ø D	102 mm
Adapter	HSK-T 63
Arbor standard	ISO 12164-3

Through-coolant	yes
Type of product	Pin vice