

Garant
eco toolholder axial single, right-hand, PSC 63, for toolholder square: 25mm


Order data

Order number	318851 25
GTIN	4045197893291
Item class	31G

Description

Version:

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT eco.

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT eco.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request. With pass-through shim. Suitable for toolholders with shank 20 and 25 mm.

Technical description

for toolholder square	25 mm
B	40 mm
Overhang dimension A	130 mm
Clamping length L ₁	102 mm
External Ø D	102 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2

Through-coolant	yes
Type of product	Pin vice