

**Garant****eco BMT transverse toolholder, BMT: 55/E****Order data**

Order number	319886 55/E
GTIN	4045197877406
Item class	31V

**Description****Version:**

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Spring-mounted pressure pad for uniform clamping of the turning tools. Perfectly matched for the respective lathe. With secured ball injection nozzles up to 80 bar. Burnished for better corrosion protection.

Suitable for efficient cooling systems such as GARANT eco, but also for other systems. Suitable for conventional toolholders.

**Application:**

Primarily for facing and internal machining.

**Technical description**

L <sub>2</sub>	64 mm
h <sub>1</sub>	20 mm
b <sub>2</sub>	45 mm
x	95 mm

Suitable machines	Emag VL, Emag VT
L <sub>1</sub>	64 mm
h <sub>2</sub>	91 mm
Type of product	Steel toolholder