

**Garant****Arbor for screw-in milling cutters with thread vibration damped, SK 40,  
Thread M×length L1: M8X75****Order data**

Order number	301307 M8X75
GTIN	4045197889195
Item class	31A

**Description****Version:**

Tapered design.

**Vibration damped version, arbor with vibration-damping core.****Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

Thread M	M8×75
External Ø D	23 mm
Bore Ø D <sub>1</sub> tolerance IT6	8.5 mm
Ø D <sub>2</sub>	13 mm
Overhang dimension A	94 mm
L <sub>2</sub>	5 mm
Reach L <sub>1</sub>	75 mm
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor

## Accessories

Pull studsealed, form A suitable for steep tapers 40	308610 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studsealed suitable for steep tapers 40	308635 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
	308630 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Pull studMazak, form A suitable for steep tapers 40M	308670 40M
--	------------

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
---	-----------

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
---	-----------

Pull studsealed, form B suitable for steep tapers 40	308650 40
--	-----------

Pull studForm A suitable for steep tapers 40	308600 40
--	-----------

Pull stud 60°sealed suitable for steep tapers 40	308785 40
--	-----------

Pull studsealed suitable for steep tapers 40	308660 40
--	-----------

Pull stud 45°sealed suitable for steep tapers 40	308765 40
--	-----------