

Garant

Arbor for screw-in milling cutters with thread vibration damped, SK 40, Thread M×length L1: M12X100



Order data

Order number	301307 M12X100
GTIN	4045197889331
Item class	31A

Description

Version:

Tapered design.

Vibration damped version, arbor with vibration-damping core.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

Bore $\varnothing D_1$ tolerance IT6	12.5 mm
External $\varnothing D$	33 mm
Thread M	M12×100
Overhang dimension A	119 mm
Reach L_1	100 mm
$\varnothing D_2$	21 mm
L_2	5 mm
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor

Accessories

Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
	308615 40

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40

Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40