

## Garant

### Arbor for screw-in milling cutters with thread vibration-damped, tapered form, HSK-A 63, Thread M×length L1: M8X100



#### Order data

Order number	307037 M8X100
GTIN	4045197905109
Item class	31A

#### Description

##### Version:

With RFID/Balluffchip bore. Tapered design. **Vibration damped version, arbor with vibration-damping core.**

##### Application:

To take screw-in milling cutters with thread.

##### Optional extras:

Extensions No. 301342, reducers No. 301344, coolant tube No. 309880, coolant tube socket wrench No. 309890.

##### Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

#### Technical description

Reach L <sub>1</sub>	100 mm
Overhang dimension A	126 mm
Bore Ø D <sub>1</sub>	8.5 mm
Ø D <sub>2</sub>	13 mm
External Ø D	23 mm
L <sub>2</sub>	5 mm

Thread M	M8×100
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor