



Clamping head smooth, SK 100, Clamping \varnothing (1 mm increments): 16mm



Order data

| | |
|--------------|---------------|
| Order number | 329950 16 |
| GTIN | 2050001924230 |
| Item class | 33H |

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping \varnothing when ordering.**

Smooth version for precision machining.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|------------------------|--------|
| Clamping \varnothing | 16 mm |
| Hardness | 60 HR |
| Profile | round |
| Clamping face | smooth |
| Length L | 59 mm |

| | |
|-----------------|------------------|
| Version | without fittings |
| Adapter | SK 100 |
| Type of product | Clamping head |