



## Clamping head smooth, SK 100, Clamping $\varnothing$ (1 mm increments): 40mm



### Order data

Order number	329950 40
GTIN	2050001924476
Item class	33H

### Description

#### Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping  $\varnothing$  when ordering.**

Smooth version for precision machining.

#### Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

Clamping $\varnothing$	40 mm
Hardness	60 HR
Profile	round
Clamping face	smooth
Length L	59 mm

Version	without fittings
Adapter	SK 100
Type of product	Clamping head