



Clamping head smooth, SK 100, Clamping \varnothing (1 mm increments): 44mm



Order data

Order number	329950 44
GTIN	2050001924513
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping \varnothing when ordering.**

Smooth version for precision machining.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	44 mm
Clamping face	smooth
Hardness	60 HR
Profile	round
Length L	59 mm

Version	without fittings
Adapter	SK 100
Type of product	Clamping head