



Clamping head with transverse and longitudinal serrations, SK 100, Clamping \varnothing (1 mm increments): 88mm



Order data

Order number	329954 88
GTIN	2050001925817
Item class	33H

Description

Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping \varnothing when ordering.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Clamping heads for special profiles to your individual requirements on request.

Technical description

Clamping \varnothing	88 mm
Profile	round
Hardness	60 HR
Clamping face	Transverse and longitudinal serrations

Length L	59 mm
Adapter	SK 100
Type of product	Clamping head