



Clamping head with transverse and longitudinal serrations, SK 100, Clamping Ø (1 mm increments): 89mm



Order data

Order number	329954 89
GTIN	2050001925824
Item class	33H

Description

Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping Ø when ordering.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Clamping heads for special profiles to your individual requirements on request.

Technical description

Clamping Ø	89 mm
Hardness	60 HR
Profile	round
Clamping face	Transverse and longitudinal serrations

Length L	59 mm
Adapter	SK 100
Type of product	Clamping head