



Clamping head soft, SK 100, Initial bore \varnothing : 30mm



Order data

Order number	329956 30
GTIN	2050001925954
Item class	33H

Description

Version:

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping \varnothing when ordering.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Clamping heads for special profiles to your individual requirements on request.

Technical description

Initial bore \varnothing	30 mm
Hardness	60 HR
Profile	round
Length L	59 mm
Adapter	SK 100

Type of product

Clamping head