

STARCKE®**Paper velour-backed abrasive disc (A), Ø 150 mm, Grit: 240****Order data**

| | |
|--------------|---------------|
| Order number | 567725 240 |
| GTIN | 4002748779343 |
| Item class | 56Z |

Description**Version:**

Abrasive thickness 540 FK (F paper, 40 to 180 grit) to thickness 544 C3K (240 – 400 grit, stearate coated) with **high strength and dense distribution**. High removal rates due to specially treated abrasive grit (**A**).

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

Application:

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

General purpose for grinding metal, non-ferrous metals, varnish, paint, wood, and plastic.

Note:

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

Technical description

| | |
|--------|--------|
| Grit | 240 |
| Disc Ø | 150 mm |

| | |
|---|-----------------------------|
| Manufacturer's designation | 544 C3K |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 150 mm |
| Propulsive equipment | Angle grinder |
| maximum circumferential speed | 40 m/s |
| Type of product | Velour-backed abrasive disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

| | |
|--|------------|
| Hook and loop backing pad,M14 External Ø 150 mm | 567760 150 |
| Hook and loop polishing pad,M14 External Ø 150 mm | 567762 150 |
| Hand sanding block with hook and loop fastening suitable for disc Ø 150 mm | 567857 150 |
