



## Abrasive cloth (A) blue, normal KK 24, 230×280 mm, Grit: 180



### Order data

Order number	556800 180
GTIN	4018875000823
Item class	56V

### Description

#### Version:

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **No fraying, very high performance and long working life**. Sheet size 230×280 mm.

Type **VSM KK 24: Blue fabric, low cost abrasive cloth** for normal applications.

#### Application:

Universally applicable, primarily for rubbing down by hand (for rubber sanding block see No. 557600).

### Technical description

Grit designation	fine
Grit	180
Manufacturer's designation	KK 24
Series	KK24
Grinding media	Standard Aluminium Oxide
Grinding medium code	A
Sanding disc width	280 mm

Sanding disc length	230 mm
Product name attribute	230×280 mm
Type of product	Abrasive cloth

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

## Accessories

Steel backing plate	556950
Rubber sanding block	557600