

**STARCKE®**
**Paper velour-backed abrasive disc (A) 8 holes, Ø 125 mm, Grit: 120**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 567745 120    |
| GTIN         | 4002748776618 |
| Item class   | 56Z           |

**Description**
**Version:**

**Abrasive paper** thickness 540 FK (F-paper, 40 to 180 grit) or thickness 544 C3K (240 – 800 grit, stearate coated) with **high strength and dense distribution**.

High material removal rates due to specially treated abrasive grit **(A)**.

The **back of the disc is covered with velour loops which automatically cling on** allowing quick disc change.

With 8-hole perforations for Bosch PEX 125, AEG EXE 400, Metabo SXE 125 with dust extraction.

**Application:**

**General purpose** for grinding metal, non-ferrous metals, varnish, paint, wood, and plastic.

On **orbital sanders** with hook and loop pads e.g. No. 567885 / 567990. Maximum circumferential speed **40 m/s**.

**Technical description**

|   |         |
|---|---------|
| Grit                                    | 120     |
| Disc Ø                                  | 125 mm  |
| Grinding medium code                    | A       |
| Iron, sulphur and chlorine constituents | < 0.1 % |

|                                 |                             |
|---------------------------------|-----------------------------|
| Product name attribute          | Ø 125 mm                    |
| Number of dust extraction holes | 8                           |
| Propulsive equipment            | Orbital sander              |
| maximum circumferential speed   | 40 m/s                      |
| Type of product                 | Velour-backed abrasive disc |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable only under restricted conditions |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable only under restricted conditions |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| Uni                            | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

|   |            |
|---|------------|
| Multi-hole PU backing pad External Ø 123 mm | 567990 123 |
|---|------------|

