

**STARCKE®**
**Paper velour-backed abrasive disc (A) 8 holes, Ø 125 mm, Grit: 320**

**Order data**

Order number	567745 320
GTIN	4002748776649
Item class	56Z

**Description**
**Version:**

**Abrasive paper** thickness 540 FK (F-paper, 40 to 180 grit) or thickness 544 C3K (240 – 800 grit, stearate coated) with **high strength and dense distribution**.

High material removal rates due to specially treated abrasive grit **(A)**.

The **back of the disc is covered with velour loops which automatically cling on** allowing quick disc change.

With 8-hole perforations for Bosch PEX 125, AEG EXE 400, Metabo SXE 125 with dust extraction.

**Application:**

**General purpose** for grinding metal, non-ferrous metals, varnish, paint, wood, and plastic.

On **orbital sanders** with hook and loop pads e.g. No. 567885 / 567990. Maximum circumferential speed **40 m/s**.

**Technical description**

Grit	320
Disc Ø	125 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Product name attribute	Ø 125 mm
Number of dust extraction holes	8
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

## Accessories

Multi-hole PU backing pad External Ø 123 mm	567990 123
---	------------

