



Spring force gauge Medio Line Newton, maximum weighing range: 25N



Order data

Order number	479417 25
GTIN	7612348400256
Item class	47F

Description

Version:

Precision balances with high accuracy $\pm 0.3\%$ of the load. Taring range up to 20% of the capacity. Any measuring position (apart from No. 479410 - only vertical). Zeroing and 20 % tare via the adjustment screw. Top and bottom mountings can be rotated by 360°.

Supplied with:

Plastic case and instruction manual.

Optional extras:

Conversion kit into spring force gauge No. 479421.

Technical description

Load capacity	Hook
Graduation	0.2 N
maximum weighing range	25 N
Scale length	100 mm
Calibration	K1

Type of product	Spring balance
-----------------	----------------

Services

CalibrationSpring balance Type F	027730 F
----------------------------------	----------

Accessories

Compression set Type MEDIO	479421 MEDIO
----------------------------	--------------

Memory pointer Type MEDIO	479429 MEDIO
---------------------------	--------------

Hook and clipfor Micro / Medio	479428
--------------------------------	--------