

## Thread "Go" / "No Go" plug gauge MultiCheck, Thread: M5



### Order data

Order number	486510 M5
GTIN	2050001060785
Item class	48B

### Description

**Version:**

Similar to No. 486000 and 486100.

Robust, easy-grip steel body with calibrated aluminium slide for measurement and direct reading of the **thread depth up to 4xD**.

**Advantage:**

Checking the thread gauge conformity and the thread depth in a single operation. Time saved for one inspection task up to 50%. Easy replacement of a worn gauge head (fitting kit on request).

**Standard:**

Toleranzen und Abmaße nach **DIN ISO 1502**.

**Note:**

MultiCheck for coarse and fine threads, with vernier (reading to 0.1mm) or with digital display (reading to 0.01mm) including data output available **on request** (see No. 486511 – 486516).

### Technical description

Thread	M5
Thread pitch	0.8 mm

Scale divisions	0.5 mm
Thread type	M
Standard	DIN 13
Type of gauge	"No Go" gauge
Type of gauge	"Go" plug gauge
Calibration	Price on request
Type of product	Thread Go / NoGo plug gauge

### Services

maximum Ø 60 mm	028650 60
-----------------	-----------