

Thread "Go" / "No Go" plug gauge MultiCheck, Thread: M8



Order data

| | |
|--------------|---------------|
| Order number | 486510 M8 |
| GTIN | 2050001060808 |
| Item class | 48B |

Description

Version:

Similar to No. 486000 and 486100.

Robust, easy-grip steel body with calibrated aluminium slide for measurement and direct reading of the **thread depth up to 4xD**.

Advantage:

Checking the thread gauge conformity and the thread depth in a single operation. Time saved for one inspection task up to 50%. Easy replacement of a worn gauge head (fitting kit on request).

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

MultiCheck for coarse and fine threads, with vernier (reading to 0.1mm) or with digital display (reading to 0.01mm) including data output available **on request** (see No. 486511 – 486516).

Technical description

| | |
|--------------|---------|
| Thread | M8 |
| Thread pitch | 1.25 mm |

| | |
|-----------------|-----------------------------|
| Scale divisions | 0.5 mm |
| Standard | DIN 13 |
| Thread type | M |
| Type of gauge | "No Go" gauge |
| Type of gauge | "Go" plug gauge |
| Calibration | Price on request |
| Type of product | Thread Go / NoGo plug gauge |

Services

| | |
|-----------------|-----------|
| maximum Ø 60 mm | 028650 60 |
|-----------------|-----------|