

STARCKE®**Abrasive paper pack, 50 pieces no holes, Grit: 120****Order data**

Order number	557571 120
GTIN	4002748356230
Item class	56Z

Description**Version:**

Flexible B or C paper, containing latex, spread with Aluminium Oxide (542B7 / 542C7). **Back with hook and loop fastener** for quick change of sheets and high tear resistance.

Advantage:

For sanding wood and painted surfaces

- **Outstanding grit bonding – long service life, no premature grit break-away damage to surfaces.**
- **Dust-repellent additives prevent clogging with grinding dust.**
- **High-quality Aluminium Oxide grit for max. grinding performance right to the end.**

Application:

For manual use with hand sanding block No. 557550 size140.

Grinding of primed paintwork, fillers, finish paintwork together with deburring and roughening of plastic components and general preparation of wood.

Technical description

Grit	120
Grit designation	medium
Width	67 mm
Length	140 mm
Type of product	Hook-and-loop sandpaper

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable only under restricted conditions		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
Steel < 55 HRC	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Ergonomic hand sanding block Length 140 mm	557550 140
Combi hand sanding blockhard / soft Length 140 mm	557555 140