

**3M****Soft-Pad set, 20 pieces soft, 140×115×5 mm, Grit: 60**

## Order data

Order number	557545 60
GTIN	4046719201662
Item class	53M

## Description

**Version:**

**Soft-Pad** with foam structure for **pressure distribution**. Coated with aluminium oxide grit (A). Coated on 1 side.

**Advantage:**

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

**Application:**

**Finish grinding of contours, edges, and at inaccessible places**, e.g. cleaning and preparation for painting. For wet and dry grinding.

## Technical description

Grit	60
Grit designation	medium
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Width	115 mm

Height	5 mm
Length	140 mm
Product name attribute	140×115×5 mm
Number of sponges, pads	20
Type of product	Abrasive sanding sponge

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		