

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260321 12/07
GTIN	4045197877765
Item class	21T

Technical description

Centre offset L_3	8.5 mm
Pack of insert screws	269028 7
Setting angle κ	107.5 degrees
Clamping height L_2	11.6 mm
Minimum pre-drill $\varnothing D_{\min}$	16 mm
ISO code toolholder	E12M SDQCR/L07
Insert size	7 mm
Overall length L	150 mm
suitable indexable insert	DC.. 0702..
Shank $\varnothing D_s$	12 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500