

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

| | |
|--------------|---------------|
| Order number | 260321 20/11 |
| GTIN | 4045197877789 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| Overall length L | 250 mm |
| suitable indexable insert | DC.. 11T3.. |
| ISO code toolholder | E20S SDQCR/L11 |
| Insert size | 11 mm |
| Clamping height L ₂ | 18.9 mm |
| Setting angle κ | 107.5 degrees |
| Pack of insert screws | 269028 8 |
| Minimum pre-drill $\varnothing D_{\min}$ | 25 mm |
| Centre offset L ₃ | 12.5 mm |
| Shank $\varnothing D_s$ | 20 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 8xD |
| Tool material | Carbide |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Set of insert screws Type 8 | 269028 8 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |