

## Garant

### Boring bar, steel, right-hand, Shank $\varnothing$ / insert size: 10/07 mm



#### Order data

Order number	260340 10/07
GTIN	4045197877796
Item class	21T

#### Description

Boring bar, steel 10/07 mm Shank  $\varnothing$   $D_s$ : 10 mm  
 ISO code toolholder: A10K SDQCR/L07  
 Setting angle  $\kappa$ : 107.5°  
 suitable indexable insert: DC.. 0702..  
 Minimum pre-drill  $\varnothing$   $D_{min}$ : 14 mm  
 Centre offset  $L_3$ : 7 mm

#### Technical description

Clamping height $L_2$	9 mm
Overall length $L$	125 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A10K SDQCR/L07
Minimum pre-drill $\varnothing$ $D_{min}$	14 mm
Insert size	7 mm
Centre offset $L_3$	7 mm
Overhang $L_1$	30 mm
Setting angle $\kappa$	107.5°
Pack of insert screws	269028 7
Shank $\varnothing$ $D_s$	10 mm
Application type	right-hand

Boring depth up to	3xD
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Set of insert screws 10 pieces	269413
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7