

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	260340 12/07
GTIN	4045197877802
Item class	21T

**Technical description**

Insert size	7 mm
Overall length L	140 mm
Setting angle $\kappa$	107.5 degrees
Overhang $L_1$	36 mm
Clamping height $L_2$	11 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A12L SDQCR/L07
Minimum pre-drill $\varnothing D_{\min}$	17 mm
Centre offset $L_3$	9 mm
Pack of insert screws	269028 7
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500