

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	260340 16/07
GTIN	4045197877819
Item class	21T

Technical description

Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Centre offset L_3	11 mm
Clamping height L_2	14 mm
Setting angle κ	107.5 degrees
suitable indexable insert	DC.. 0702..
Overall length L	180 mm
Pack of insert screws	269028 7
ISO code toolholder	A16Q SDQCR/L07
Overhang L_1	48 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500